



X9500



- 1: Fill Cap 2: Black Lid 3: BPA free Container
- 4: Blades assembly 5: Retainer Nut
- 6: Drive Socket 7: Switch panel 8: Cushion Pad
- 9: Rubber feet 10: Motorbase
- 11: Overloading switch

### Specifications

Size	190 * 190 * 440 mm
Weight	6.0 kg
Power	2380 W 4.0 HP
Speed	RPM: 45000
Material	Plastic/ Steel
Knives	Carbon Steel
Controls	Touch
Noise reduction	Yes - Pad
CE Certificate	Yes
Container	2.0 l. BPA free



This blender is equipped with an electronic glass touch keypad.

The keypad has a main power On/Off button, and High Middle and Low, 7 function setting timer and Pulse buttons.

Press the On/Off button, to turn on the blender. The whole glass pad will illuminate.

For continuous operation, press either Low or Middle or High button, When finished blending, Press stop.

For momentary operation, press the pulse button, motor will run on High speed until the button is released.

Also you can press setting, choose the best function for your food blend. Each function will have difference speed and time.

To turn the unit off, press On/Off button. Blue LED light will go off.

This blender is equipped with a pulse option. Hold paddle switch in down position to engage pulse function. Unit will run on high speed until the paddle switch is released.

Motor must come to a complete stop before removing container from blender base. Never place the container on the motor base or remove it from the motor base while motor is running.

Always hold container with one hand when starting and while blending. Never operate without jar lid.

Wash and dry container after each use.